



## WL350 COUNTER TOP DRAWING AND PARTS LIST

### Wetted Parts



Yellow = Consumables

Green = Recommended spare parts



No	WLCP Part No	Description	Factory PN	Stocked?	
<b>Consumables</b>					
1	12-8310	15W UV Lamp Assembly	CT-2085-A	Yes	
2	FT-0063-IL Assy with FT-0064 Element	1-micron 10" Inline CBC Filter for CTO, Lead, Cyst and Asbestos Reduction (Carbon Block) <b>Required for NSF Certification</b>	FT-0063-IL Assy with FT-0064 Element	Yes	
<b>Recommended Spare Parts</b>					
3	12-1500	Solenoid Valve 1000mm (recommend replacing Solenoid Cushion at same time)  <i>Recommend stocking 2 each for every 10 units purchased</i>	PU-4016	Yes	
3.1	CU-0001	Solenoid Cushion  <i>Recommend stocking 2 each for every 10 units purchased</i>	CU-0001	Yes	
4	12-8370	Hot Water Faucet  <i>Recommend stocking 2 each for every 10 units purchased</i>	PL-1351	Yes	
5	12-8305	Quartz Spiral for Firewall  <i>Recommend stocking 1 each for every 10 units purchased</i>	FU-0007	Yes	
6	12-8355	Main PCB  <i>Recommend stocking 2 each for every 10 units purchased</i>	EN-6126-L00-00	Yes	
7	12-8056	Silicon Button Key Mat  <i>Recommend stocking 2 each for every 10 units purchased</i>	PL-1153	Yes	
8	12-8057	Button Label  <i>Recommend stocking 2 each for every 10 units purchased</i>	LP-7084	Yes	
9	12-8150	Drip Tray Grill – Charcoal  <i>Recommend stocking 2 each for every 10 units purchased</i>	PL-1152	Yes	

10	12-8055	Drip Tray - Charcoal with Waterlogic Logo  <i>Recommend stocking 2 each for every 10 units purchased</i>	PL-1156	Yes	
11	12-8300	UVC Sensor  <i>Recommend stocking 2 each for every 10 units purchased</i>	AK-0063	Yes	
12	12-5615	Hot Tank 1.6 Liter (.42 gallon) 100V / 500W Factory Set Point 185°F - 85°C  <i>Recommend stocking 2 each for every 10 units purchased</i>	HT-3041	Yes	
12.1	12-6900	Thermostat and Overload Metal Cover  <i>Recommend stocking 2 each for every 10 units purchased</i>	ST-8290	Yes	
13	12-1360	Overload with Manual reset - 105°C (221° F)  <i>Recommend stocking 2 each for every 10 units purchased</i>	HT-3012	Yes	
14	12-1303	Hot Tank Thermostat - (87°C) 187° F  <i>Recommend stocking 2 each for every 10 units purchased</i>	HT-3013A	Yes	
15	12-8315	UV 15 W 120V/60Hz Electronic Ballast  <i>Recommend stocking 2 each for every 10 units purchased</i>	EN-0008-L01-00	Yes	
16	12-8365	Firewall UV Relay PCB  <i>Recommend stocking 2 each for every 10 units purchased</i>	EN-6127	Yes	
Not Shown	01-2076	Scale Kleen <i>Recommend stocking 5 each</i>	NA	Yes	
<b>Remaining Parts</b>					
17	NA	Metal Cover – Counter Top Only	ST-0049-L00-00	No	

18	Purchase from John Guest	1/4" Union Elbow John Guest P/N P10308S	PU-4008-A	No	
19	Purchase from John Guest	3/4" Union Tee John Guest P/N P10208S	PU-4011-A	No	
20	12-8375	Transformer 1.6A / 120 V for Firewall – <b>Counter Top Only</b>	EL-5147	Yes	
21	NA	2L (.5G) Cold Tank Assembly No UV holder, No sub-tank <b>Counter Top Only</b>	CT-2060-B	No	
22	12-3165	Upper Shelf - <b>Counter Top Only</b>	ST-8150	Yes	
23	20-0075	Energy Saver PCB	EN-6131	Yes	
24	NA	Electric Ballast Bracket	ST-0059-L00-00	No	
25	Purchase from John Guest	JG 1/4" Stopper PI0808S (used with Bulkhead Union 1/4" x 1/4" John Guest P/N PI1208S) – <b>Counter Top Only</b>	PU-4086	No	
26	10-3067	Bulkhead Union 1/4" x 1/4" John Guest P/N PI1208S	PU-4028-A	Yes	
27	12-8062	Side Panel - <b>Counter Top Only</b>	ST-8245	Yes	
28	10-3095	CDS Fixing Rubber (Silicon)	CT-2010	Yes	
29	12-8320	Firewall UV Lamp Rubber	CT-2088	Yes	

30	12-8325	Spiral Rubber Buffer	CT-2077	Yes	
31	12-8330	Firewall Mark IV Stainless Assembly (No internal components)	FU-0008-A	Yes	
32	12-8360	Front Upper Insert Panel <i>Sold Separately:</i> 12-8056 Silicon Button Key Mat 12-8057 Button Label	PL-1359	Yes	
33	12-8350	Firewall PCB Cover	PL-1357	Yes	
34	12-8345	Silver Front Panel for Drip Tray Insert-Firewall	PL-1146-A	Yes	
35	Purchase from John Guest	JG 3/8" x 1/4" Reducing Fitting(PI211208S)	PU-4137	No	
36	NA	Firewall Solenoid Valve Fixing Bracket - <b>Counter Top Only</b>	ST-8297	No	
37	NA	Filter Bracket - <b>Counter Top Only</b>	ST-8152-A	No	
38	12-3150	Unit Rubber Feet – <b>Counter Top Only</b>	PL-1251-CN	Yes	
39	12-3170	Bottom Tray - <b>Counter Top Only</b>	ST-8151-A	Yes	
40	12-3155	Leak Tray – <b>Counter Top Only</b>	PL-1294	Yes	

41	12-3180	Leak Containment Tray Clip (sensor 0.5mm)	ST-8207-CN	Yes	
41.1	NA	Leak Sensor Wire – <b>Counter Top Only</b>	EL-5076-KR	No	
42	10-2200	Compressor (R134a 1/8HP) 120V/60Hz	CO-9001-A	Yes	
42.1	10-3003	Compressor Starter Relay	CO-9016	Yes	
42.2	10-5018	Compressor Overload	CO-9015	Yes	
43	19-1069	Cold Tank Thermostat (recommend to replace 48.1 Cold Thermostat Cover Label as well)	CT-2070-A	Yes	
43.1	LP-0326	Cold Thermostat Cover Label	LP-0326-L00-00	Yes	
44	10-4013	Socket - Power Line Noise Filter, Electromagnetic Interference filter (EMI)	EL-5016	Yes	
45	10-3014	Fuse Holder and Fuse 120V / 15A with One Wire	EL-5053	Yes	
45.1	10-3013	Fuse 120V / 15A	EL-5010	Yes	
46	10-3008	Red Compressor & Heater Switch	EL-5004	Yes	
47	12-8061	Silver Back Panel - <b>Counter Top Only</b>	ST-8216	No	
48	12-8060	Flat Top Cover - Charcoal with Texture – <b>Counter Top Only</b>	PL-1249-CN	Yes	



49	12-3100	Wire Condenser – <b>Counter Top Only</b>	CO-9031	Special Order	
49.1	12-0001	Filter Dryer	CO-0008	Yes	
50	10-7040	Silicon Tube 5/16" for Hot Water	PU-4064	Yes	
51	Purchase from John Guest	JG LLD PE Tube - Blue O.D.1/4"John Guest P/N PE-08-BI-1000F-B	PU-4031-A	No	
52	Purchase from John Guest	JG Equal Straight Connector 1/4"(PI0408S)	PU-4010	No	
53	20-1015	Filter Bracket - <b>Counter Top Only</b>	ST-8326	Yes	
54	20-1010	2.8" Filter Clip	PU-4161	Yes	
55	AK-0014-B	Flow Restrictor (1.8 mm hole)	AK-0014-B	Yes	
Not Shown	12-8335	Firewall UV Female Wire & Connector	EL-5141-A	Yes	
Not Shown	NA	Wire Connector between Hot Tank and Thermostat	EL-5142	Special Order	
Not shown	10-3007	Power Cord 120V – 1840 mm	EL-5001-B	Yes	
Not shown	10-3017	PCB Stand-off Pin	EN-6059	Yes	
Not shown	12-5252	Wire Harness Set	EN-5057-CN	Yes	